**Data Sheet** 

# 9861 Series

### **Thermal Mass Flow**

# High Temperature Mass Flow Controllers/Meters

### **Overview**

Originally developed by Unit Instruments (later Celerity Inc.), the 9861 Series of high temperature mass flow controllers and meters continue to be manufactured using the same supply chain and copy exact process by Brooks Instrument who acquired the IP and assets of Celerity Inc. in 2009.

The 9861 Series remains the optimum choice for critical precursor and dopant vapor delivery in semiconductor and optical fiber manufacturing.

### **Product Description**

The 9861 Series are thermal mass flow controllers and meters designed for challenging high temperature delivery of condensable precursors and dopants.

A high purity, high leak integrity metal flow path ensures compatibility with all processes gases and vapors. The patented IsoSensor™ is a high stability flow sensor compatible with the elevated environmental temperatures found in heated gas lines and baking systems (temperature-controlled gas boxes). The ultra-low drift performance of the IsoSensor reduces the need for frequent re-zeroing and recalibration typical in high temperature applications.

For maximum flexibility and inventory reduction, the 9861 Series remote electronics come standard with two analog electrical connectors (a 20 pin card edge and a 9 or a 15 pin "D" connector option) and Semi industry standard RS485 digital communication enabling easy retrofit and standardization.

In mass flow controller models, a diaphragm free solenoid control valve provides a wide dynamic control range for superior precision and control. Designed for long-term reliability, the valve has been marathon tested to over 8 million cycles with no degradation in performance.

#### **Model** Description


9861 Ultra-High Purity Digital Mass Flow Controller with Analog and RS485 interfaces







### **Features and Benefits**

Features	Benefits						
High temperature mass flow controller	Reliable delivery of condensable gases and precursors						
Digital measurement and control architecture	Enhanced accuracy and process control						
Ultra-High purity flow path	Ensures integrity and purity of gas/vapor						
Ultra-stable flow measurement sensor	Reduced maintenance for superior uptime and lowest cost of ownership						
Upstream pressure buffering (optional)	Stable mass flow delivery under challenging supply conditions						
All metal diaphragm free control valve	Enhanced long-term reliability						
Dual I/O interfaces	Universal upgrade enabling standardization and inventory reduction						





### **Product Dimensions**



# Product Specifications

Performance Specifications								
Settling Time (to within 2% of setpoint)	· · · · · · · · · · · · · · · · · · ·							
Fast Start	$\leq$ 1.0 sec (per SEMI E17-91)							
Soft Start	Linear 20% per sec (0 to 100% in 5 sec)							
Accuracy (N, equivalent)								
35% to 100% F.S.	±1% setpoint (per SEMI E56-96)							
< 35% F.S.	±0.35% full scale (per SEMI E56-96)							
Repeatability (full scale)	±0.15% (per SEMI E56-96)							
Linearity (full scale)	±0.5% (per SEMI E27-92)							
Inlet Pressure Coefficient	0.007% per psi (N <sub>2</sub> )							
Ambient Temperature Coefficient								
Zero	0.05% full scale per °C							
Span	0.1% full scale per °C							
Leak Integrity	1 x 10 <sup>-10</sup> atm-cc/sec (He) (per SEMI E16-90)							
Automatic Zero	Optional (customer programmable)							
Zero Drift	$\leq$ 0.6% per year without auto-zero							
Thermal Siphoning and Attitude Sensitivity	< 0.1% full scale (30 psi SF,)							
Operating Limits								
Standard Flow Range	3 sccm to 10 slm (N <sub>2</sub> equivalent)							
Control Range (full scale)	2-100%							
Valve Leak Rate	≤1% full scale							
Gases	All							
Ambient Temperature Range	0-150°C (32-302°F)							
Maximum Operating Pressure	620 kPa (90 psi)							
Differential Operating Pressure (Typical)	1.33-350 kPa (10 torr - 50 psia)							
Warm-up Period	30 minutes							
Mounting Position	HOV or HOS							
Valve	Normally closed solenoid							
Electrical Characteristics								
Input/Output Signal	0 E V/de linearly proportional to required flow							
Setpoint Input Output Monitor	0-5 Vdc linearly proportional to required flow 0-5 Vdc linearly proportional to flow rate							
Digital Input/Output	RS485L (via R]11 ports)							
Valve Off	External: TTL signal							
Auto shut-off	Setpoint < 2% full scale commands valve off							
Power								
Controller (RS485)	+15 Vdc (160 mA max.), -15 Vdc (160 mA max.)							
Meter (Analog)	+15 Vdc (50 mA max.), -15 Vdc (50 mA max.)							
Power Consumption	9861 = 5 watts max.							
Mechanical Characteristics								
Surface Finish	4μ inch Ra							
Fittings	1/4" VCR <sup>®</sup> , 3/8" VCR <sup>®</sup>							
Valve Position	Downstream							
Materials	Wetted Components: 316L SS/KM-45/304/7MO+							
Weight	1.2 kg (2.65 lbs)							
Calibration References								
Traceability	National Institute of Standards and Technology (N.I.S.T.)							
Standard Temperature and Pressure	0°C and 760 mm Hg per (SEMI E 12-96)							

Specifications and features are subject to change without notice.

# Model Code - 9861 Series

C       Mass Flow Controller         Mass Flow Meter         9861       Ultra-High Purity, Metal Seal, RS485 Digital and Analog Interface         Auto Shut-off         X       Auto Shut-off         No Auto Shut-off         F       Fast Start 1 Second Response         5       Second Linear Soft Start         T       6-10 Second Soft Start         X       No Valve (Meter)         XXXX XXXX       Specify Pre-programmed Gas and Full Scale Range         (example: Nitrogen = "0013"; 90sccm= "090C")         4R       1/4" VCR         3/8" VCR         HOV       Horizontal or Vertical Mounting Attitude (Standard)
9861       Ultra-High Purity, Metal Seal, RS485 Digital and Analog Interface         A       Auto Shut-off         X       No Auto Shut-off         F       Fast Start 1 Second Response         5       Second Linear Soft Start         6-10 Second Soft Start         X       No Valve (Meter)         XXXX XXXX       Specify Pre-programmed Gas and Full Scale Range (example: Nitrogen = "0013"; 90sccm= "090C")         4R       1/4" VCR         3/8" VCR         HOV       Horizontal or Vertical Mounting Attitude (Standard)
A       Auto Shut-off         X       No Auto Shut-off         F       Fast Start 1 Second Response         5       Second Linear Soft Start         T       6-10 Second Soft Start         X       No Valve (Meter)         XXXX XXXX       Specify Pre-programmed Gas and Full Scale Range (example: Nitrogen = "0013"; 90sccm= "090C")         4R       1/4" VCR         3R       3/8" VCR         HOV       Horizontal or Vertical Mounting Attitude (Standard)
X       No Auto Shut-off         F       Fast Start 1 Second Response         5       Second Linear Soft Start         6-10 Second Soft Start         X       No Valve (Meter)         XXXX XXXX       Specify Pre-programmed Gas and Full Scale Range (example: Nitrogen = "0013"; 90sccm= "090C")         4R       1/4" VCR         3R       3/8" VCR         HOV       Horizontal or Vertical Mounting Attitude (Standard)
F       Fast Start 1 Second Response         5       Second Linear Soft Start         T       6-10 Second Soft Start         X       No Valve (Meter)         XXXX XXXX       Specify Pre-programmed Gas and Full Scale Range (example: Nitrogen = "0013"; 90sccm= "090C")         4R       1/4" VCR 3R         3/8" VCR         HOV       Horizontal or Vertical Mounting Attitude (Standard)
S       5 Second Linear Soft Start         G-10 Second Soft Start         X       No Valve (Meter)         XXXX XXXX       Specify Pre-programmed Gas and Full Scale Range (example: Nitrogen = "0013"; 90sccm= "090C")         4R       1/4" VCR         3R       3/8" VCR         HOV       Horizontal or Vertical Mounting Attitude (Standard)
T       6-10 Second Soft Start         No Valve (Meter)         XXXX XXXX       Specify Pre-programmed Gas and Full Scale Range (example: Nitrogen = "0013"; 90sccm= "090C")         4R       1/4" VCR         3R       3/8" VCR         HOV       Horizontal or Vertical Mounting Attitude (Standard)
X       No Valve (Meter)         XXXX XXXX       Specify Pre-programmed Gas and Full Scale Range (example: Nitrogen = "0013"; 90sccm= "090C")         4R       1/4" VCR         3R       3/8" VCR         HOV       Horizontal or Vertical Mounting Attitude (Standard)
XXXX XXXX       Specify Pre-programmed Gas and Full Scale Range (example: Nitrogen = "0013"; 90sccm= "090C")         4R       1/4" VCR         3R       3/8" VCR         HOV       Horizontal or Vertical Mounting Attitude (Standard)
(example: Nitrogen = "0013"; 90sccm= "090C")  4R 1/4" VCR 3R 3/8" VCR  HOV Horizontal or Vertical Mounting Attitude (Standard)
4R       1/4" VCR         3R       3/8" VCR         HOV       Horizontal or Vertical Mounting Attitude (Standard)
3R       3/8" VCR         HOV       Horizontal or Vertical Mounting Attitude (Standard)
HOV Horizontal or Vertical Mounting Attitude (Standard)
HOS Horizontal or Side
A Atmospheric Downstream Pressure
V Vacuum Downstream Pressure
MM Metal O-Ring/ Metal Seat
MX Metal O-Ring- No Valve (Meter)
T 9 Pin "D" Connector & 20 Pin Card Edge Connector & Dual RJ11 ports, 0-5 VDC
U 15 Pin "D" Connector & 20 Pin Card Edge Connector & Dual RJ11 ports, 0-5 VDC
XXXX Customer Special Request (CSR)
C Normally Closed (Standard)
X No Valve (Meter)
S Standard (Valve Downstream)
X No Valve (Meter)
A Auto-Zero Enabled
X Auto-Zero Disabled
04E 4µ inch Ra Finish
0°C Reference
Calibration (Standard)
XX Custom Reference
Calibration (20°C=20)

Sample Model Code
-------------------

с	9861	Α	F	XXXX XXXX	4R	ноу	Α	мм	T	XXXX	с	S	A	04E	00	
---	------	---	---	-----------	----	-----	---	----	---	------	---	---	---	-----	----	--

# Notes

### **Brooks Service and Support**

Brooks is committed to assuring all of our customers receive the ideal flow solution for their application, along with outstanding service and support (All Brooks products including Tylan, Tylan General, Millipore, Mykrolis, UNIT and Celerity branded products). We operate first class repair facilities located around the world to provide rapid response and support. Each location utilizes primary standard calibration equipment to ensure accuracy and reliability for repairs and recalibration and is certified by our local weights and measures authorities and traceable to the relevant international standards.

Visit www.BrooksInstrument.com to locate the service location nearest to you.

#### START-UP SERVICE AND IN-SITU CALIBRATION

Brooks Instrument can provide start-up service prior to operation when required. For some process applications, where ISO-9001 quality certification is important, it is mandatory to verify and/or (re)calibrate the products periodically. In many cases this service can be provided under in-situ conditions, and the results will be traceable to the relevant international quality standards.

#### CUSTOMER SEMINARS AND TRAINING

Brooks Instrument can provide customer seminars and dedicated training to engineers, end users and maintenance persons.

Please contact your nearest sales representative for more details.

Due to Brooks Instrument's commitment to continuous improvement of our products, all specifications are subject to change without notice.

#### TRADEMARKS

Brooks, Celerity, IsoSensor, Tylan, Tylan General, UNIT ...... Brooks Instrument, LLC All others are the property of their respective owners.



Global Headquarters Brooks Instrument 407 West Vine Street Hatfield, PA 19440-0903 USA Toll-Free (USA): 888-554-FLOW T: 215-362-3500 F: 215-362-3745 BrooksAM@BrooksInstrument.com

A list of all Brooks Instrument locations and contact details can be found at www.BrooksInstrument.com



©Copyright 2017 Brooks Instrument, LLC All rights reserved. Printed in U.S.A.