Advanta Sil[®]

APSW 4-Ply, Wire-Reinforced, Mandrel-Wrapped, Silicone Suction Hose Platinum-Cured; Smooth or Convoluted O.D.

TECH SHEET



ow volatile grade, platinum-cured silicone hose for critical pharmaceutical, biopharm, cosmetic, and food applications comprises the liner of AdvantaSil APSW. The liner is slipped onto a mandrel and wrapped with polyester mesh fabric, 316 stainless steel reinforcing wire and additional silicone. It is then cured into a homogeneous hose, enhancing its pressure and vacuum capabilities. AdvantaSil APSW has undergone extensive physical, chemical and biological testing and meets USP Class VI, FDA CFR 177.2600, ISO 10993 and European Pharmacopoeia 3.1.9 standards.

Key Features

- Available with a smooth O.D. or, for easier bending, convoluted O.D.
- Two construction styles offered: standard linear wrapped or spiral wrapped for higher warking processory on improved range of flag



APSW-P & APSW-PC only

- working pressures, an improved range of flexibility and availability in larger sizes
 Low volatile grade silicone suitable for pharmaceutical, biopharm, cosmetic, and food applications such as ultrapure water transfer, food processing, washdown stations, skid systems, and other suction and discharge uses
- Hardness value of 70 Shore A
- Rated for full vacuum
- Crush and kink resistant; durable and heavy-duty
- AdvantaSil APSW has a Master File with the U.S. Food and Drug Administration (#27582)
- Linear wrapped styles (APSW-P and APSW-PC) are listed by the National Sanitation Foundation for food equipment materials (NSF-51)
- Liner certified free of animal-derived ingredients
- General temperature range: -100°F (-73.3°C) to 350°F (176.6°C)
- Resists temperature extremes, chemical attack, ozone, radiation, moisture and environmental exposure
- Sterilizable by autoclave, CIP and SIP processes
- Documented lot traceable with identification on packaging
- Documented quality control per ISO 9001:2015

Complete validation package available on request



E

о е

b u r

ർ

dvant


ww.a

 $\overline{\mathbb{C}}$

MARINA MARIA

AdvantaSil APSW hose is not intended for implantation and is not to be used for continuous steam applications.





Advanta Sil[°] APSW 4-Ply, Wire-Reinforced, Mandrel-Wrapped, Silicone Suction Hose



SP<u>ECIFICATIONS</u>

Dusdust	Nominal t I.D. O.D.				Working Vacuum Pressure			Burst Pressure Minimum				iaht (14 I I
Product Number	(in.)	(mm)		.D. (mm)	Rating		ssure '0°F	at 7		Bend		0	Standard Length
Tumber	(111.)	(11111)			(in./Hg.		1°C)		1°C)	Radius		Meter	
			(1010		(· · · ·		(PSI)			(lb)	(kg)	(100)
APSW-P -	– Ѕмо	отн ().D. ,	LINEA	R W	RAPPE	ED						
APSW-P-0500	.500	12.70	.910	23.11	>29	150	10.3	600	41.4	2.0	.281	.418	13
APSW-P-0750	.750	19.05	1.16	29.46	>29	150	10.3	600	41.4	2.5	.359	.534	13
APSW-P-1000	1.000	25.40	1.41	35.81	>29	150	10.3	600	41.4	3.5	.438	.652	13
APSW-P-1500	1.500	38.10	1.91	48.51	>29	150	10.3	600	41.4	4.0	.685	1.019	13
APSW-P-2000	2.000	50.80	2.41	61.21	>29	150	10.3	600	41.4	6.0	.875	1.302	13
APSW-PC	с — С	ONVOL	UTED	O.D.	LINE	EAR W	RAPI	PED					
APSW-PC-0500	.500	12.70	.910	23.11	>29	150	10.3	600	41.4	2.0	.208	.309	13
APSW-PC-0750	.750	19.05	1.16	29.46	>29	150	10.3	600	41.4	2.5	.307	.457	13
APSW-PC-1000	1.000	25.40	1.41	35.81	>29	150	10.3	600	41.4	3.5	.390	.580	13
APSW-PC-1500	1.500	38.10	1.91	48.51	>29	150	10.3	600	41.4	4.0	.625	.930	13
APSW-PC-2000	2.000	50.80	2.41	61.21	>29	125	8.6	500	34.5	6.0	.775	1.153	13
APSW-SP	- SN	IOOTH	O.D	., Spir	AL W	RAPP	ED						
APSW-SP-0500	.500	12.70	.910	23.11	>29	380	26.2	1520	104.8	1.0	.281	.418	12
APSW-SP-0750	.750	19.05	1.16	29.46	>29	315	21.7	1260	86.9	1.5	.359	.534	12
APSW-SP-1000	1.000	25.40	1.41	35.81	>29	250	17.2	1000	68.9	2.5	.438	.652	12
APSW-SP-1500	1.500	38.10	1.91	48.51	>29	250	17.2	1000	68.9	4.0	.685	1.019	12
APSW-SP-2000	2.000	50.80	2.41	61.21	>29	205	14.1	820	56.5	6.0	.875	1.302	12
APSW-SP-2500	2.500	63.50	2.91	73.91	>29	185	12.8	740	51.0	10.5	1.050	1.562	12
APSW-SP-3000	3.000	76.20	3.41	86.61	>29	190	13.1	760	52.4	CF	1.230	1.830	12
APSW-SP-4000	4.000	101.60	4.41	112.01	>29	140	9.7	560	38.6	CF	1.710	2.545	12

Nominal wall dimensions for all sizes and styles: .205"; 5.21mm Custom lengths and hose assemblies with an assortment of fittings are available. CF = Consult Factory

NOTE: When products are used as part of an assembly, the pressure ratings of fittings may be less than hose pressure ratings above. Please consult your sales representative.



©2019 NewAge® Industries, Inc. Specifications are subject to change without notice. AdvantaPure produces are produced by NewAge® Industries, Inc. AdvantaSilw, NewAge Industries AdvantaPure®, Purity in Fluid FlowSystems®, NewAge®, and the "N" logo are registered trademarks of NewAge® Industries, Inc.

WARRANTY: NewAge industries AdvantaPure products are warranted to be free from defects in material and workmanship. Any product found to carry such defects will be replaced without charge. This warranty is limited only to the replacement of NewAge Industries AdvantaPure products, term for item, which after examination by NewAge Industries AdvantaPure are detective. NewAge Industries AdvantaPure specifically disclaims any other liability. The data supplied is provided as a helpful guideline and is believed to be reliable; however, nothing stated shall constitute a guarantee, recommendation, or warranty for any application. NOTCE: NewAge Industries, inc. has been a privately owned corporation since 1954. Neither the corporation are its provided are a filiated, in any wey, with any other group or entity either representing themselves as or being referred to by the term New-Age.

JILIGONE